

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

Olympus Water Immersion Objectives [See More by Olympus](#)



- Water Immersion Objectives with Excellent DIC and Fluorescence
- Displays Flat Images From High Transmission Factors up to the Near-Infrared Region of the Spectrum
- Ideal for Fluorescence Imaging of Tissue and Specimens, such as Brain Tissue
- Magnification Ranges from 10X to 60X

Common Specifications

General

Compatible Tube Lens Focal Length (mm):	Focal Length: 180mm	Manufacturer:	Olympus
--	---------------------	---------------	---------

Optical Properties

Compatible Cover Glass Thickness (mm):	N/A	Wavelength Range (nm):	400 - 700
Field Number (mm):	26.5	Parfocal Length (mm):	45
Immersion Liquid:	Water		

Threading & Mounting

Mounting Threads:	RMS / 20.32mm x 36 TPI
-------------------	------------------------

Technical Information

Products

Magnification	NA	Field Number (mm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
10X	0.30	26.5	18.00	1- U2M583	3.5	#34-555	₹1,01,700	1 In Stock
20X	0.50	26.5	9.00	1- U2M585	3.5	#34-556	₹1,98,450	2 In Stock
40X	0.80	26.5	4.50	1- U2M587	3.3	#34-557	₹3,06,000	3 In Stock
60X	1.00	26.5	3.00	1- U2M592	2.00	#73-282	₹3,88,350	1 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com