




NOTES:

1. SUBSTRATE: Polymer Film XP40HT-18
2. WAVELENGTH RANGE: 400 - 700 nm
3. POLARIZATION EFFICIENCY (%): >99.5
4. TRANSMISSION (%):
 SINGLE: 40 ±2
 PARALLEL: 32.2
 CROSSED: <0.005
5. EXTINCTION RATIO: 5000:1
6. TEMPERATURE RESISTANCE (°C x HOURS):
 HEAT: 100 x 1,000
 COLD: -40 x 1,000
 HUMIDITY: 80 x 90% RH x 1,000
7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY



| | | | | |
|------------------------|----|--------|---|---------------|
| THIRD ANGLE PROJECTION | | TITLE | 12.5mm Dia. High-Temperature Linear Polarizing Film (XP40HT-18) | |
| ALL DIMS IN | mm | DWG NO | 29465 | SHEET 1 OF 12 |