

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Laser Mirrors](#)
TECHSPEC® Precision Ultraviolet Mirrors


- 120nm and 190nm Design Wavelengths
- Average Reflectivity >85% Across Specified Range
- Enhanced Metallic Coatings for Broadband Reflectivity through the Visible Region

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	90
---------------------	----

Optical Properties

Surface Flatness (P-V):	$\lambda/10$
-------------------------	--------------

Substrate:	Fused Silica (Corning 7980)
------------	---



Coating Type:	Metal
---------------	-------

Angle of Incidence (°):	0
-------------------------	---


Material Properties

Vacuum Compatibility:	10^{-7} Torr
-----------------------	----------------

Technical Information



Precision Ultraviolet Mirrors



Products

Dia. (mm)	Surface Flatness (P-V)	Coating Specification	Coating	AOI (°)	Thickness (mm)	Stock Number	Price	Buy
5.00	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	2.00	#18-725	₹19,463 Volume Pricing	14 In Stock
10.00	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	2.00	#18-726	₹20,241 Volume Pricing	20+ In Stock
12.50	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	6.00	#33-912	₹21,020 Volume Pricing	7 In Stock
15.00	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	3.00	#18-727	₹21,409 Volume Pricing	14 In Stock
20.00	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	3.00	#18-728	₹22,187 Volume Pricing	5 In Stock
25.00	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	6.00	#33-913	₹22,187 Volume Pricing	20+ In Stock
30.00	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	5.00	#18-729	₹22,966 Volume Pricing	9 In Stock
35.00	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	5.00	#18-730	₹23,355 Volume Pricing	20+ In Stock
40.00	λ/10	R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	5.00	#18-731	₹24,523 Volume Pricing	20+ In Stock

50.00	$\lambda/10$	$R_{avg} \geq 78\% @$ 120 - 125nm $R_{avg} \geq 85\% @$ 120 - 600nm	Enhanced Aluminum (120- 600nm)	0	10.00	#33-914	₹29,583 Volume Pricing	12 In Stock
5.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	2.00	#18-739	₹21,409 Volume Pricing	12 In Stock
10.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	2.00	#18-740	₹22,187 Volume Pricing	10 In Stock
12.50	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	6.00	#18-741	₹22,577 Volume Pricing	2 In Stock
12.50	$\lambda/10$	$R_{avg} > 88\% @$ 190 - 195nm $R_{avg} > 85\% @$ 200 - 600nm	Enhanced Aluminum (190- 600nm)	0	6.00	#48-567	₹19,852 Volume Pricing	20+ In Stock
15.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	3.00	#18-742	₹22,966 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	3.00	#18-743	₹23,744 Volume Pricing	13 In Stock
25.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	6.00	#18-744	₹24,523 Volume Pricing	11 In Stock
25.00	$\lambda/10$	$R_{avg} > 88\% @$ 190 - 195nm $R_{avg} > 85\% @$ 200 - 600nm	Enhanced Aluminum (190- 600nm)	0	6.00	#48-568	₹21,409 Volume Pricing	20+ In Stock
30.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	5.00	#18-745	₹24,912 Volume Pricing	11 In Stock
35.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	5.00	#18-746	₹26,469 Volume Pricing	10 In Stock

40.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	5.00	#18-747	₹27,637 Volume Pricing	12 In Stock
50.00	$\lambda/10$	$R_{avg} \geq 92\% @$ 190 - 250nm $R_{avg} \geq 83\% @$ 250 - 900nm	Enhanced Aluminum (190- 900nm)	0	10.00	#18-748	₹31,062 Volume Pricing	20+ In Stock
50.00	$\lambda/10$	$R_{avg} > 88\% @$ 190 - 195nm $R_{avg} > 85\% @$ 200 - 600nm	Enhanced Aluminum (190- 600nm)	0	10.00	#48-569	₹26,858 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
 Phone: 1-800-363-1992 :
www.edmundoptics.com