

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [UV and IR Windows](#)
TECHSPEC® Lithium Fluoride (LiF) Windows


- High Transmission from 150nm - 6μm
- Excellent Vacuum UV (VUV) Transmission
- Low Index of Refraction

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Edges:	Fine Ground
Knoop Hardness (kg/mm²):	102.00	Parallelism (arcmin):	<3
Poisson's Ratio:	0.33	Young's Modulus (GPa):	64.97


Optical Properties

Abbe Number (v_d):	97.29	Axis Orientation:	Random
Coating:	Uncoated	Substrate:	Lithium Fluoride (LiF)
Surface Quality:	60-40	Wavelength Range (nm):	150 - 6000

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):	37	Density (g/cm³):	2.64
---	----	------------------------------------	------

Technical Information



Products

Dia. (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
5.00	1.00	Uncoated	#19-724	₹9,169 Volume Pricing	7 In Stock
10.00	1.00	Uncoated	#19-725	₹11,809 Volume Pricing	1 In Stock
12.50	1.00	Uncoated	#19-726	₹15,624 Volume Pricing	1 In Stock
12.70	1.00	Uncoated	#16-804	₹15,624 Volume Pricing	2 In Stock
20.00	2.00	Uncoated	#19-727	₹21,712 Volume Pricing	9 In Stock
25.00	2.00	Uncoated	#19-728	₹23,105 Volume Pricing	4 In Stock
25.40	1.00	Uncoated	#16-805	₹25,526 Volume Pricing	5 In Stock
50.00	3.00	Uncoated	#19-729	₹56,480 Volume Pricing	5 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com