


[All Products](#) /
 [Optics](#) /
 [Polarization Optics](#) /
 [Linear Polarizers](#) /
 [Absorptive \(Dichroic\) Polarizers](#) /
 [Polymer Film Polarizers](#)

Super High Contrast Polarizing Film



- Exceptional Contrast of 15,000:1 in the Visible Spectrum
- Available with or without Adhesive Backing
- Circular and Rectangular Geometries
- For Superior Contrast see [TECHSPEC Ultra-High Contrast Polarizing Film \(XP42HE\)](#)

Common Specifications

Physical & Mechanical Properties

Construction: Polarizing Film

Optical Properties

Extinction Ratio: 15,000:1 nominal

Substrate: Cellulose Triacetate Film

P-Polarization Transmission (%): >42

Wavelength Range (nm): 400 - 700

Environmental & Durability Factors

Operating Temperature (°C): -20 to +70

Technical Information

Products

Dimensions (mm)	Dia. (mm)	Stock Number	Price	Buy
990 x 620	-	#26-916	₹68,897 Volume Pricing	1 In Stock
990 x 620	-	#26-917	₹68,897 Volume Pricing	1 In Stock
25 x 25	-	#26-918	₹2,024 Volume Pricing	5 In Stock
50 x 50	-	#26-919	₹2,803 Volume Pricing	20+ In Stock
100 x 100	-	#26-920	₹4,437 Volume Pricing	15 In Stock
200 x 200	-	#26-921	₹9,731 Volume Pricing	20+ In Stock
-	12.50	#26-922	₹1,635 Volume Pricing	20+ In Stock
-	25.00	#26-923	₹2,024 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com