

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [UV and IR Windows](#)
TECHSPEC® Barium Fluoride (BaF₂) Windows


- Excellent Transmission from 200nm - 12μm
- Resistant to High-Energy Radiation
- Provide High Transmission without AR Coatings

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Edges:	Fine Ground
Knoop Hardness (kg/mm²):	82.00	Parallelism (arcmin):	<3
Poisson's Ratio:	0.34	Young's Modulus (GPa):	53


Optical Properties

Abbe Number (v_d):	81.78	Index of Refraction (n_d):	1.48
Substrate:	Barium Fluoride (BaF ₂)	Surface Quality:	60-40


Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):	18.1	Density (g/cm³):	4.89
---	------	------------------------------------	------

Technical Information



Infrared AR Coated Barium Fluoride Windows 3mm Thickness



Products

Dia. (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
5.00	1.00	Uncoated	#87-699	₹8,582 Volume Pricing	1 In Stock
12.50	2.00	Uncoated	#87-700	₹12,616 Volume Pricing	15 In Stock
25.00	3.00	Uncoated	#87-701	₹19,658 Volume Pricing	4 In Stock
25.40	3.00	Uncoated	#18-362	₹19,658 Volume Pricing	16 In Stock
50.00	3.00	Uncoated	#87-702	₹47,311 Volume Pricing	14 In Stock
50.80	3.00	Uncoated	#18-363	₹47,311 Volume Pricing	10 In Stock
5.00	1.00	BBAR (2000-5000nm)	#23-526	₹12,029 Volume Pricing	5 In Stock
12.50	2.00	BBAR (2000-5000nm)	#23-527	₹15,990 Volume Pricing	11 In Stock
12.70	2.00	BBAR (2000-5000nm)	#23-528	₹15,990 Volume Pricing	5 In Stock
25.00	3.00	BBAR (2000-5000nm)	#23-529	₹23,105 Volume Pricing	7 In Stock
25.40	3.00	BBAR (2000-5000nm)	#23-530	₹23,105 Volume Pricing	5 In Stock
50.00	3.00	BBAR (2000-5000nm)	#23-531	₹51,345 Volume Pricing	3 In Stock
50.80	3.00	BBAR (2000-5000nm)	#23-532	₹51,345 Volume Pricing	3 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com