

[All Products](#) / [Optics](#) / [Prisms](#) / [Image Rotation Prisms](#)

TECHSPEC® Schmidt-Pechan Prisms



- Provides Inline Image Rotation of 180°
- Compact Design for OEM Integration
- Air Spaced for Optimal Performance

Common Specifications

Physical & Mechanical Properties


Dimensional Tolerance (mm): ± 0.1

Optical Properties


Coating: VIS 0° & Aluminized

Substrate:	N-BK7	Surface Quality:	40-20
Image Orientation:	Right-Handed	Coating Specification:	Entrance/Exit Faces: $R_{avg} \leq 0.4\%$ @ 425 - 675nm Roof: $R_{avg} > 85\%$ @ 400 - 700nm w/Black Overpaint
Ray Deviation (°):	0	Wavelength Range (nm):	400 - 700
Ray Deviation Tolerance (arcmin):	± 10	Power (fringes) @ 632.8nm:	1.00
Irregularity (fringes) @ 632.8nm:	0.25		


Technical Information




#36-038



#36-039



Schmidt-Pechan Prism Ray Path



Schmidt-Pechan Prism Tunnel Diagram

Products

Width (mm)	Height (mm)	Coating	Wavelength Range (nm)	Stock Number	Price	Buy
14.00	20.2	VIS 0° & Aluminized	400 - 700	#36-038	₹36,990 Volume Pricing	3 In Stock
29.00	50.45	VIS 0° & Aluminized	400 - 700	#36-039	₹46,350 Volume Pricing	3 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com