

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Off-Axis Mirrors](#)**TECHSPEC®**

Off-Axis Parabolic Mirrors with Alignment Through Holes



- Through Holes Parallel to Focused and Collimated Beams
- Range of Metallic Coatings Available
- $<50\text{\AA}$ RMS Surface Roughness

Common Specifications


Physical & Mechanical Properties


Diameter (mm):	25.40 +0.00/-0.10	Surface Roughness (Å):	<50 RMS
Y Offset (mm):	25.40	Through Hole Orientation:	1 x Parallel to Focused Beam 1 x Parallel to Collimated Beam
Through Hole Diameter (mm):	4.1		

Optical Properties

Effective Focal Length EFL (mm):	25.40	Radius of Curvature (mm):	25.40
Focal Length Tolerance (%):	±1	Off-Set Angle (°):	90
Coating Type:	Metal	Surface Figure, RMS:	λ/8
Parent Focal Length PFL (mm):	12.7	Substrate:	Aluminum 6061-T6
Surface Quality:	80-50		

Technical Information





Products

Dia. (mm)	EFL (mm)	Coating	Off- Set Angle (°)	Surface Roughness (Å)	Stock Number	Price	Buy
25.40	25.40	Enhanced Aluminum (250-700nm)	90	<50 RMS	#11-768	₹21,020 Volume Pricing	3 In Stock
25.40	25.40	Protected Aluminum (400- 2000nm)	90	<50 RMS	#11-770	₹20,241 Volume Pricing	4 In Stock
25.40	25.40	Protected Gold (700- 10000nm)	90	<50 RMS	#11-772	₹25,924 Volume Pricing	7 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
 Phone: 1-800-363-1992 :
www.edmundoptics.com