

12mm Dia. x 24mm FL, NIR II Coated, DCX N-K5 Lens



Stock **#67-624** CLEARANCE CONTACT US

-

1

+

₹1,910

ADD TO CART

Volume Pricing	
Qty 1+	₹1,910 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Double-Convex Lens

Type:

Physical & Mechanical Properties

12.00 +0.00/-0.10

Diameter (mm):

<1	Centering (arcmin):
4.00 ±0.05	Center Thickness CT (mm):
2.50	Edge Thickness ET (mm):
11	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

24.00 @ 587.6nm	Effective Focal Length EFL (mm):
22.65	Back Focal Length BFL (mm):
NIR II (750-1550nm)	Coating:
R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm	Coating Specification:
N-K5	Substrate: ☐
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1.00	Focal Length Tolerance (%):
2.00	f/#:
0.25	Numerical Aperture NA:
750 - 1550	Wavelength Range (nm):
8 J/cm² @ 1064nm, 10ns	Damage Threshold, By Design: ☐


Regulatory Compliance

Compliant	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- N-K5 Substrate
 - Various Anti-Reflection (AR) Coatings
 - PCX and DCX Options Available
- N-K5 Lenses are available in various diameters, focal lengths, as well as Plano-Convex and Double-Convex form factors. Anti-reflective coatings covering the VIS to NIR make these ideal for multiple applications.

TECHNICAL INFORMATION



COMPATIBLE MOUNTS

