


[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Plate Beamsplitters](#)

VIS-NIR Polka-Dot Beamsplitters



- 50/50 and 30/70 Reflection/Transmission Ratios Available
- B270 Substrates for High Performance from 400 – 2000nm
- [UV-NIR](#) Versions Available

Common Specifications

Physical & Mechanical Properties

Center to Center Spacing (mm):	0.15	Clear Aperture (%):	90
Construction:	Polka-Dot	Parallelism (arcmin):	<3
Thickness (mm):	1.65 ±0.1		


Optical Properties

Angle of Incidence (°):	0 - 45		
Coating:	Square Aluminum (AlMgF ₂) Apertures	Minimum Aperture (mm):	2.00
Reflection/Transmission Tolerance (%):	±5 @ 45°	Substrate:	B270
Surface Quality:	80-50	Wavelength Range (nm):	400 - 2000

Environmental & Durability Factors

Operating Temperature (°C):	150 Maximum
-----------------------------	-------------

Technical Information



Products

Dia. (mm)	Dimensions (mm)	Substrate	Reflection/Transmission Ratio (R/T)	Wavelength Range (nm)	Thickness (mm)	Stock Number	Price	Buy
12.70	-	B270	50/50	400 - 2000	1.65	#15-983	₹11,070 Volume Pricing	20+ In Stock
-	12.7 x 12.7	B270	50/50	400 - 2000	1.65	#15-982	₹11,070 Volume Pricing	4 In Stock
25.40	-	B270	30/70	400 - 2000	1.65	#15-985	₹12,690 Volume Pricing	6 In Stock
-	25.4 x 25.4	B270	30/70	400 - 2000	1.65	#15-984	₹12,690 Volume Pricing	5 In Stock
25.40	-	B270	50/50	400 - 2000	1.65	#15-981	₹12,690 Volume Pricing	3 In Stock
-	25.4 x 25.4	B270	50/50	400 - 2000	1.65	#15-980	₹12,690 Volume Pricing	7 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com