

TECHSPEC[®] 6.25mm Dia x -6.25mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC[®] Illumination Grade PCV Cylinder Lenses

Stock **#46-191** **5 In Stock**

-

1

+

₹4,788

ADD TO CART

Volume Pricing	
Qty 1-5	₹4,788 each
Qty 6-25	₹4,282 each
Qty 26-49	₹4,087 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Cylinder Lens, Plano-Concave

Type:

Physical & Mechanical Properties

	Diameter (mm):
6.25 +0.0/-0.2	
	Center Thickness CT (mm):
1.00	
	Center Thickness Tolerance (mm):
±0.1	
	Edge Thickness ET (mm):
3.38	

Optical Properties

	Effective Focal Length EFL (mm):
-6.25	
	Substrate:
N-BK7	
	f#:
1.00	
	Numerical Aperture NA:
0.50	
	Coating:
Uncoated	
	Wavelength Range (nm):
350 - 2200	
	Back Focal Length BFL (mm):
-6.91	
	Focal Length Tolerance (%):
±3	
	Radius R ₁ (mm):
-3.24	
	Surface Quality:
60-40	


Regulatory Compliance

	RoHS 2015:
Compliant	
	Reach 224:
Compliant	
	Certificate of Conformance:
View	

PRODUCT DETAILS

- Cylinder Lenses Ideal for 1 Dimensional Laser Beam Convergence
 - Circular and Rectangular Form Factors
 - Multiple Coating Options Available
- TECHSPEC® Illumination Grade PCV Cylinder Lenses are commonly used to turn a collimated laser source into a line generator. These PCV Cylinder Lenses and [TECHSPEC Illumination Grade PCX Cylinder Lenses](#) can be used together for beam expander applications.
- The thin lens approximation for the length of a line generated by a negative cylinder lens is: $L = 2 * (r_0/f) * (z + f)$ where L is the line length, r_0 is half the beam diameter, z is the projection distance, and -f is the focal length of the lens.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
-