

TECHSPEC[®] 25.4mm Dia. 320 - 450nm Broadband $\lambda/10$ Mirror



Stock #39-390 12 In Stock

-

1

+

₹10,121

ADD TO CART

Volume Pricing	
Qty 1-5	₹10,121 each
Qty 6-25	₹8,096 each
Qty 26-49	₹7,590 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Flat MirrorType:


Physical & Mechanical Properties	
25.40 +0.00/-0.10	Diameter (mm):
Commercial Polish	Back Surface:
90	Clear Aperture (%):
Ground, 0.5mm max bevel	Edges:
<3	Parallelism (arcmin):
6.35 ±0.20	Thickness (mm):
Optical Properties	
Dielectric Mirror (320-450nm)	Coating:
Coating Specification: R _{avg} >98% @ 340 - 488nm (0°, All Polarizations) R _{avg} >98% @ 320 - 450nm (45°, All Polarizations) R _{avg} >99% @ 320 - 450nm (45°, S-Polarization)	
320 - 450	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Fused Silica (Corning 7980)	Substrate: ☐
20-10	Surface Quality:
Dielectric	Coating Type:
0-45	Angle of Incidence (°):
0.5 J/cm² @ 355nm, 20ns, 20Hz	Damage Threshold, By Design: ☐
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

PRODUCT DETAILS

- Enhanced Reflectivity and LIDT over Metallic Coatings
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Designed for all Polarization States from 0 – 45° AOI

TECHSPEC® Broadband Dielectric λ/10 Mirrors are ideal for beam steering or reflection applications utilizing multiple laser sources. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. The highly durable fused silica substrate offers a low thermal expansion coefficient and a high abrasion resistance. TECHSPEC® Broadband Dielectric λ/10 Mirrors are designed for applications from the UV to the near-infrared spectra.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS
