

Polarization Maintaining Optical Fiber, PANDA, 620-850nm, 5m



Stock #72-906 NEW 3 In Stock

₹8,953

ADD TO CART

Volume Pricing

Qty 1+	₹8,953 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

PM Type:

Physical & Mechanical Properties

125.0 ± 1.0 Cladding Diameter (µm):

5	Length (m):
3.5	Core Diameter (μm):
245.0 ± 15.0	Coating Diameter:
Optical Properties	
0.12	Numerical Aperture NA:
≤ 15.0 dB/km @ 630 nm	Attenuation (dB/km):
620 - 850	Wavelength Range (nm):
4.5 ± 0.5 @ 630 nm	Mode Field Diameter (nm):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are cladded step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with core diameters of 3.0μm up to 8.2μm and numerical apertures ranging from 0.12 to 0.14.