



- NOTES:
- 1. SUBSTRATE: UV FUSED SILICA
  - 2. ROHS COMPLIANT
  - 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: ENHANCED ALUMINUM  
Ravg >95% @ 450 - 650nm

S2: NONE



4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                     | S1                  | S2                  |
|---------------------|---------------------|---------------------|
| SHAPE               | PLANO               | PLANO               |
| ANGLE TOL. (arcsec) | ±15                 | ±15                 |
| SURFACE QUALITY     | 20-10               | 20-10               |
| SURFACE FLATNESS    | λ/20                | λ/20                |
| BEVEL               | PROTECTED AS NEEDED | PROTECTED AS NEEDED |

|  |    |        |   |
|--|----|--------|---|
|  Edmund Optics®         |    |        |   |
| THIRD ANGLE PROJECTION  |    | TITLE  | 25mm Enhanced Aluminum Coated, UV Fused Silica Right Angle Mirror |
| ALL DIMS IN  | mm | DWG NO | 22550   |
|  |    |        | SHEET 6 OF 18   |