



NOTES:
1. SUBSTRATE:
SCHOTT D 263®T ECO

2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: PROTECTED ALUMINUM (400-700nm)
R(AVG) ≥85% @ 400 - 700nm @ 45° AOI
S2: NONE

3. CUT SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	22.50 x 22.50	22.50 x 22.50
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

TITLE	25mm Sq., 0.1mm Thick, Protected Aluminum, Ultra-Thin Mirror		
DWG NO	70094	SHEET 2 OF 4	