


[All Products](#) / [Testing and Detection](#) / [Amplifiers](#)

Dual Phase Lock-In Amplifier



- Dual Phase Operation with Modulus(R) Calculation
- Differential or Single-Ended Input
- Gain Setting from $3\mu\text{V}$ to 1V
- High Performance Wide Bandwidth Input Gain Stage
- Analogue Meter for Display of X, Y or R Output Signals
- Separate X, Y and R Output BNCs
- X and Y Offset Controls
- Output Time Constants from $100\mu\text{s}$ to 30s
- 1F and 2F Reference Signal Operation
- 90° Step or Fine Phase Control

Technical Information



Products

Title	Stock Number	Price	Buy
10Hz to 100kHz, Dual Phase Lock-In Amplifier	#55-784	₹2,51,550	2 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com