


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Molded](#)

LightPath® Blue Laser Collimating Aspheric Lenses See More by [Lightpath®](#)



- Designs Optimized for 405nm and 488nm Laser Diodes
- Ideal for Biomedical Instrumentation and Data Storage Applications
- Diffraction Limited Molded Aspheric Lens Designs

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed

Optical Properties

Substrate: [D-Lak6](#)

Coating:	BBAR (350-600nm)	Coating Specification:	$R_{abs} < 1.0\%$ @ 350 - 600nm
Wavelength Range (nm):	350 - 600	Conjugate Distance:	Infinite

Technical Information

Products

Dia. (mm)	EFL (mm)	NA	Coating	Stock Number	Price	Buy
6.33	4.00	0.61	BBAR (350-600nm)	#83-681	₹8,910 Volume Pricing	20+ In Stock
6.33	4.02	0.60	BBAR (350-600nm)	#83-990	₹8,910 Volume Pricing	20+ In Stock
2.00	1.41	0.50	BBAR (350-600nm)	#37-108	₹8,235 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com