


TECHSPEC® 25mm Dia. 1.0° Beam Dev. Fused Silica Wedge Prism, UV-VIS Coated



TECHSPEC Fused Silica Wedge Prisms

Stock **#89-637** **5 In Stock**

⊖ 1 ⊕ ₹13,680

ADD TO CART

Volume Pricing	
Qty 1-5	₹13,680 each
Qty 6-25	₹10,980 each
Qty 26-49	₹10,260 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Wedge Prism

Type:

Note:

Specify this is S1 & S2 power and irregularity, not the overall power of the wedge

Physical & Mechanical Properties

25.00 +0.00/-0.10 **Diameter (mm):**

3.00 **Thickness (mm):**

Protective as needed **Bevel:**

2° 5'56" **Wedge Angle (arcmin):**

Optical Properties

15 **Angle Tolerance (arcsec):**

UV-VIS (250-700nm) **Coating:**

355 **Design Wavelength DWL (nm):**

Fused Silica (Corning 7980) **Substrate:**

20-10 **Surface Quality:**

Beam Deviation **Image Orientation:**

Coating Specification:
 $R_{abs} \leq 1.0\%$ @ 350 - 450nm
 $R_{avg} \leq 1.5\%$ @ 250 - 700nm

200 - 2200 **Wavelength Range (nm):**

0.50 **Power (fringes) @ 632.8nm:**

0.20 **Irregularity (fringes) @ 632.8nm:**

0 **Angle of Incidence (°):**

1.00 **Ray Deviation @ 355nm (°):**

1.74 **Power (diopters):**

2.1° **Wedge Angle (°):**

Material Properties

0.52 **Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 235:**



PRODUCT DETAILS

- Deviates Laser Beam Path from 0.5° - 5.0°
- Ideal for UV to NIR Beam Steering Applications from 250 to 1064nm
- Ideal for High Power Beam Steering Applications

TECHSPEC® Fused Silica Wedge Prisms are designed for a range of laser beam steering applications requiring UV-VIS or first through fourth Nd:YAG harmonic Anti-Reflection Coatings. They are optimized to ensure the highest level of system performance using tightly controlled specifications including $\lambda/10$ surface flatness, 20-10 surface quality, and a wedge tolerance of 15 or 30 arcseconds. The Nd:YAG coated versions feature high transmittance and guaranteed laser damage thresholds specific to the design wavelength. TECHSPEC® Fused Silica Wedge Prisms utilize a wedge design to deviate laser beam path from 0.5° – 5°. By creating a risley prism pair using two wedge prisms with the same ray deviation, custom beam steering up to two times the wedge deviation is possible. A low coefficient of thermal expansion ensures accurate beam steering in high power laser applications.

Note: Power Diopter is defined as 1cm deviation at a distance of 1m from the prism. TECHSPEC® Wedge Prisms are also available in [N-BK7 versions](#).

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).